

S1	MODE OF OPERATION	ON	OFF
S10	N/A	N/A	N/A
S9	1 OR 2PUMPS	1PUMP	2PUMPS
S8	DEG.C/ F°	C°	F°
S7	PUMP2 1SPD/2SPD	1SPD	2SPD
S6	N/A	N/A	N/A
S5	PUMP1 1SPD/2SPD	1SPD	2SPD
S4	AUX. FREEZE	MUST BE OFF	
S3	CIRC/NONCIRC	CIRC.	NONCIRC
S2	F.O. /SPA LITE	F.O.	SPA LITE
S1	30/50A	30A	50A

P/N 52294HC3  
MODEL 2000LE

**Balboa Instruments Incorporated**  
BALBOA INSTRUMENTS INC.  
TUSTIN, CA.

**LISTED** US  
74254


60 HZ

**MODEL:** DU-2000LE-DCAH

PAT. NO. 4618797

Certified to comply with the limits for a class B computing device pursuant to subpart J of part 15 of the FCC rules

Neutral WHITE	Hot BLACK	Hot RED
USE COPPER CONDUCTOR ONLY #6 AWG MIN. WIRE=60/75°C	EMPLOYER UNIQUEMENT DES CONDUCTEURS DE CUIVRE.	TORQUE RANGE FOR TB1: 21-23 IN. LBS



IF PCB HAS 9 POSITION SWITCH DISREGARD THE 10TH POSITION