

S1	MODE OF OPERATION	ON	OFF
S10	N/A	N/A	N/A
S9	1 OR 2 PUMPS	1 PUMP 2 PUMPS	2 PUMPS
S8	DEG.C./ F	2	F
S7	PUMP2 1SPD/2SPD	1SPD	2SPD
S6	N/A	N/A	N/A
S5	PUMP1 1SPD/2SPD	1SPD	2SPD
S4	AUX. FREEZE	MUST BE OFF	
S3	CIRC/NONCIRC	CIRC.	NONCIRC
S2	F.O. /SPA LITE	F.O.	SPA LITE
S1	30/50A	30A	50A

P/N 52294HC3
MODEL 2000LE

Balboa Instruments
Incorporated
BALBOA INSTRUMENTS INC.
TUSTIN, CA.



Certified to comply with
the limits for a class B
computing device pursuant
to subpart J of part 15
of the FCC rules



60 HZ

MODEL: DU-2000LE-DCAH

PAT. NO. 4618797

IF PCB HAS 9 POSITION SWITCH
DISREGARD THE 10TH POSITION

Neutral WHITE	Hot BLACK	Hot RED
USE COPPER CONDUCTOR ONLY #6 AWG MIN. WIRE=60/75°C	EMPLOYER UNIQUEMENT DES CONDUCTEURS DE CUIVRE.	TORQUE RANGE FOR TB1: 21-23 IN. LBS

